



### Model No. : OEM-Z109/SN



#### **Product Introduction**

Standard pump head with compact structure, exquisite appearance, fixed occlusion and stable running. Can stack several pump heads, and support various equipment.

#### **Typical Application**

- 1. Use in the ice cream machine and coffee making machine
- 2. Support COD on-line monitor

### Flow Data

Pump Head	Housing Material	Rollers Material	Tubing		G 1 D ()	Flow Rate	Weight (kg)
			Tubing Sizes	ID×Wall Thickness	Speed Range(rpm)	(mL/min)	weight (kg)
SN15-14	PC	304 stainless steel	14#	1.6×1.6(mm)	0.1-600	0.024 ~144	0.20
SN15-16			16#	3.1×1.6(mm)		0.088~528	
SN25			24#	6.4×2.4(mm)		0.25~1500	


# Motor Specification

Model No.	del No. OEM-JT03		
Flow rate	7.2-750mL/min		
Motor type	AC speed adjustable motor		
Voltage	AC220V(standard) DC110V(optional)		
Speed	30-300rpm		
Speed error	≤±10%		
Working environment	0-40°C, 80%RH		





# **Dimension Drawing (Unit:mm)**



## **Tubing Installation Procedure**



A. Disassemble the pump head, and press the tubing on the rollers.



B. Make the tubing go around the rollers one cycle, and merge it on the exit.



C. Tighten the tubing aptly, and load the other half pump head body.